



Heavy Duty Face Shield with Headgear . M-5002 (SafeFace)

- Shell : High Density HDPE Headgear
- Face Shield : Available for PC, PVC, Steel Mesh
- Knob : Adjustable Rotary Knob
- Sweatband : Removable & Washable Fabric
- Chin Strip : Adjustable & Removable Nylon (Optional)
- CE EN166:2002
- ANSI Z87.1-2010
- AS/NZS1337.1-2010



ADJUSTABLE
KNOB



Impact
Protection



Shock
Absorption



Adjustable
Rotary Knob



Breathable
Design



Heat
Resistant



Chemical
Resistant



Electric
Hazard



Quality
Warranty



DUST PROOF DESIGN

Block splashes and prevent dust particles



✓ Face Protection

ADJUSTABLE ROTARY KNOB DESIGN

Easy to rotate and adjust helmet size



✓ Adjustable

CHEMICAL SPUTTERING PROTECTION DESIGN

Corrosion resistant materials can resist sputtering of chemical liquids and solvents, suitable for laboratory or chemical environment



✓ Chemical Protection

Color Available: Yellow, Orange, Red etc



Users Instruction:

1.) APPLICATION AND LIMITATION OF USE

This helmet is designed to provide limited head protection by reducing the force of small falling objects striking or penetrating the top of the shell. It was not designed to provide front, side, or rear impact or penetration protection, while it may protect against light bumps to these areas.

Avoid contact of these devices with electrical wires, very low temperature (-20 °C or -30 °C and very high temperature (+150°C)

2.) PRE-USE INSPECTION

Always do a visual inspection of the helmets immediately before use to ensure that it is in a serviceable condition and operates correctly. The helmet should have no sharp, burr, damaged, missing part, cracks, nicks or breaks. To ensure the safety of users, the device should be regularly periodic examinations per a month by a competent person strictly in according with manufacturer's periodic examination procedure for continued efficiency and durability of the device.

3.) LIFESPAN

The helmet can be expected to remain in service for 5 years or more, when it is not damaged during use.

4.) CLEANING AND DISINFECTION

Clean the helmet with mild soap and lukewarm water. Do not use paints, solvents, chemicals, adhesives, gasoline or like substances on this helmet. The impact resistance and other protective properties of the helmet may be destroyed by such substances. The loss of these protective properties may not be apparent or readily detectable by the user. After each use, disinfection should be done and the use of agents that are not known to be harmful to th

5.) STORAGE

Store the helmet in a cool, dry and clean place out of direct sunlight. Avoid area where heat, moisture, light, oil, or their vapours or other degrading elements may be present.